

Two of Doc Johnson's most popular Deluxe Vac-U-Lock Sets receive a much-awaited expansion and are now available in Caramel and Chocolate in addition to Vanilla.

Each multi-piece collection includes:

- 1 patented Vac-U Plug
- 1 unisex Supreme Harness in cushioned neoprene (adjustable up to 69 in./175cm)
- Interchangeable o-rings in 3 sizes
- 1 Vac-U-Lock compatible suction cup for hands-free use
- Care and usage products
- A selection of Vac-U-Lock attachments in lifelike ULTRASKYN

Featured Products



Dual Density Starter Set
 1051-20-BX Vanilla



Dual Density Starter Set **NEW**
 1051-21-BX Caramel



Dual Density Starter Set **NEW**
 1051-22-BX Chocolate

Dual Density Starter Set

Attachments Included:

Thin Dong
 Length 7" (17.8 cm) Width 2" (5.1 cm)

Spiral Dong
 Length 6" (15.2 cm) Width 1.5" (3.8 cm)

Textured Cock
 Length 5.5" (12.7 cm) Width 1.5" (3.8 cm)



Dual Density ULTRASKYN Set
 1051-05-BX Vanilla



Dual Density ULTRASKYN Set **NEW**
 1051-06-BX Caramel



Dual Density ULTRASKYN Set **NEW**
 1051-07-BX Chocolate

Dual Density ULTRASKYN Set

Attachments Included:

Realistic Dong
 Length 8" (20.3 cm) Width 1.7" (4.3 cm)

Cock
 Length 7" (17.8 cm) Width 1.75" (4.5 cm)

Slim Cock
 Length 7" (17.8 cm) Width 1.5" (3.8 cm)

For information on the entire Vac-U-Lock line, go to docjohnson.com/vaculock

CONTACT INFO:

www.docjohnson.com

Care and Maintenance

To clean your harness, hand wash with a mild soap and cold water. Lay flat to dry. Remove vibrating component when not in use and before cleaning. To clean attachments, spray with Doc Johnson® Toy Cleaner or wash with a mild soap and warm water. Allow to dry completely before storing separately from other toys in a cool, dry place. Use with water-based lubricant/glide. *Doc Johnson® Toy Cleaner sold separately.